

Product datasheet

Specifications



Opale buzzer white

X3300WH

Main

Range	Opale
Product Or Component Type	Buzzer
Device Application	Alarm
Device Presentation	Mechanism with central plate
Quantity Per Set	Set of 1
Main Colour Tint	White

Complementary

Device Mounting	Flush
Number Of Modules	2 modules
[Ue] Rated Operational Voltage	220 V AC
Fixing Mode	By captive screws
Surface Finish	Satin
Connections - Terminals	Shrouded terminals
Height	48 mm
Width	42 mm
Depth	40.9 mm
Operating Time	60 s
Standards	IEC 62080
Clamping Connection Capacity	1.5...2.5 mm² for flexible cable(s) 1.5...2.5 mm² for rigid or stranded cable(s)
Material	ABS + PC: front cover PC: base cover
Colour Tint	White

Environment

Ip Degree Of Protection	IP20
Ambient Air Temperature For Operation	-5...35 °C
Noise Level	0...70 dB

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	4.2 cm
Package 1 Width	4.2 cm
Package 1 Length	4.2 cm
Package 1 Weight	45 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	60
Package 2 Height	150 cm
Package 2 Width	275 cm
Package 2 Length	325 cm
Package 2 Weight	2705 g

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations