

# Product datasheet

Specifications



## Wall plate, Digilink, 1 gang, shuttered

DCBRWPS1PSWT\_WE

### Main

Range	Digilink
Product Or Component Type	Wall plate
Provided Equipment	With shutter
Cover Plate Colour Tint	White

### Complementary

Number Of Gangs	1 gang
Communication Network Category	5e 6
Suitable For Connector Type	Ethernet network: keystone (Digilink) UTP
Shape Of Connector	Straight
Fixing Mode	By 2 screws
Device Mounting	Surface Flush
Material	ABS + PC
Width	86 mm
Length	86 mm
Targeted Region	Asia Pacific.

### Environment

Ip Degree Of Protection	IP21
Ambient Air Temperature For Operation	-10...50 °C
Ambient Air Temperature For Storage	-10...60 °C

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.05 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	51.35 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	20

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19.5 cm
Package 2 Weight	1.027 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	200
Package 3 Height	21 cm
Package 3 Width	32.5 cm
Package 3 Length	50 cm
Package 3 Weight	10270 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability





**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile		No need of specific recycling operations