
Product datasheet

Specifications





MODULAR FRONT PLATE W300 3M

03213

- ! Discontinued on: 30 Sept 2022
- ! End-of-service on: 25 Apr 2023
- ① Discontinued

Main

Range	Prisma	
Range Of Product	Prisma G Prisma P	
Product Or Component Type	Front plate	
Accessory / Separate Part Category	Installation accessory	
Range Compatibility	Prisma Prisma G duct Prisma Prisma P cubicle	
Type Of Front Plate	Modular Cut-out	
Installed Device	TeSys: fixed GV2L TeSys: fixed GV2LE TeSys: fixed GV2ME TeSys: fixed GV2P TeSys: fixed GV2RTn Acti 9: fixed modular device <= 40 A Multi9: fixed modular device <= 40 A TeSys: fixed GV3	
Poles Description	4 x 3P: modular rail support: GV2L 4 x 3P: modular rail support: GV2LE 4 x 3P: modular rail support: GV2ME 4 x 3P: modular rail support: GV2P 4 x 3P: modular rail support: GV2RTn 3 x 3P: modular rail support: GV3	

Complementary

Enclosure/Cubicle Description	Floor-standing duct - width 300 mm Wall-mounted duct - width 300 mm Cubicle duct - width 400 mm depth 400 mm
Connection Position	Direct connection
9 Mm Pitches	20
Number Of 18 Mm Modules Per Row	10
Number Of Vertical Modules [50 Mm]	3
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA
Material	Steel
Surface Finish	Smooth Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder

Colour	White (RAL 9001)	
Height	150 mm	
Width	300 mm	
Net Weight	0.32 kg	
Quantity Per Set	Set of 1	
Functional Unit	300 mm Prisma G floor-standing duct TeSys GV2L fixed 3P 4 direct 3 300 mm Prisma G wall-mounted duct TeSys GV2L fixed 3P 4 direct 3 300 mm Prisma G floor-standing duct TeSys GV2LE fixed 3P 4 direct 3 300 mm Prisma G wall-mounted duct TeSys GV2LE fixed 3P 4 direct 3 300 mm Prisma G floor-standing duct TeSys GV2ME fixed 3P 4 direct 3 300 mm Prisma G wall-mounted duct TeSys GV2ME fixed 3P 4 direct 3 300 mm Prisma G floor-standing duct TeSys GV2P fixed 3P 4 direct 3 300 mm Prisma G wall-mounted duct TeSys GV2P fixed 3P 4 direct 3 300 mm Prisma G wall-mounted duct TeSys GV2P fixed 3P 4 direct 3 300 mm Prisma G floor-standing duct TeSys GV2RTn fixed 3P 4 direct 3 300 mm Prisma G wall-mounted duct TeSys GV2RTn fixed 3P 4 direct 3 300 mm Prisma G wall-mounted duct TeSys GV3 fixed 3P 3 direct 5 300 mm Prisma G wall-mounted duct TeSys GV3 fixed 3P 3 direct 5 300 mm Prisma G wall-mounted duct Acti 9 modular device <= 40 A fixed 20 direct 3 400 mm 400 mm Prisma P cubicle Acti 9 modular device <= 40 A fixed 20 direct 3 300 mm Prisma G floor-standing duct Multi9 modular device <= 40 A fixed 20 direct 3 300 mm Prisma G wall-mounted duct Multi9 modular device <= 40 A fixed 20 direct 3	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.500 cm
Package 1 Width	16.000 cm
Package 1 Length	26.500 cm
Package 1 Weight	310.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	17.000 cm
Package 2 Width	17.500 cm
Package 2 Length	28.000 cm
Package 2 Weight	3.300 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	320
Package 3 Height	48.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	128.000 kg



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
Ø	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile