Product datasheet





① Discontinued

auxiliary contact, Acti9, iSD, 1OC, AC/DC

A9A26927

Discontinued on: 15 Nov 2023

Price: 12,000.00 NGN

Main

Range Of Product	Acti9
Product Or Component Type	Fault contact
Device Short Name	iSD
Signal Contacts Composition	1 C/O
[In] Rated Current	DC-12 1 A at 130 V, DC
	DC-12 1.5 A at 60 V, DC
	DC-12 2 A at 48 V, DC
	DC-12 6 A at 24 V, DC
	AC-12 3 A at 415 V, AC 50/60 Hz
	AC-12 6 A at 240 V, AC 50/60 Hz
9 Mm Pitches	1

Complementary

[Ui] Rated Insulation Voltage	500 V
[Uimp] Rated Impulse Withstand Voltage	4 kV
Local Signalling	Mechanical indicator
Mounting Mode	Clip-on
Mounting Support	DIN rail
Comb Busbar And Distribution Block Compatibility	Top: YES
Height	86 mm
Width	9 mm
Depth	73 mm
Net Weight	33 g
Colour	White
Connections - Terminals	Screw clamp terminal (bottom) 2 cable(s) 2.5 mm² - rigid Screw clamp terminal (bottom) 2 cable(s) 1.5 mm² - flexible with ferrule Screw clamp terminal (bottom) 1 cable(s) 0.52.5 mm² - flexible Screw clamp terminal (bottom) 1 cable(s) 14 mm² - rigid
Wire Stripping Length	10 mm
Tightening Torque	1 N.m

Environment

Standards	EN/IEC 60947-5-1
Ip Degree Of Protection	IP20 conforming to EN/IEC 60947-5-1

Life Is On Schneider 23 Apr 2024

Pollution Degree	3 conforming to EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Ambient Air Temperature For Operation	-3570 °C
Ambient Air Temperature For Storage	-4085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.800 cm
Package 1 Width	2.000 cm
Package 1 Length	9.200 cm
Package 1 Weight	40.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.500 cm
Package 2 Width	10.000 cm
Package 2 Length	27.500 cm
Package 2 Weight	570.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	120
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	6.373 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
②	Mercury Free	
	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information