



ZCKD21 nebuvo pakeistas. Norėdami gauti daugiau informacijos, susisiekite su Klientų aptarnavimo centru.

⚠ Nutraukta

Main

| | |
|---------------------------|---|
| Range of product | OsiSense XC |
| Series name | Standard format |
| Product or component type | Limit switch head |
| Device short name | ZCKD |
| Head type | Plunger head |
| Product compatibility | XCKL XCKM |
| Associated body | ZCKL1 ZCKL1H7 ZCKL5 ZCKL5H7 ZCKL6 ZCKL6H7 ZCKL7 ZCKL7H7 ZCKL8 ZCKL8H7 ZCKLD31 ZCKLD31H7 ZCKLD35 ZCKLD35H7 ZCKLD37 ZCKLD37H7 ZCKLD39 ZCKLD39H7 ZCKM1 ZCKM1H29 ZCKM1H7 ZCKM5 ZCKM5H29 ZCKM5H7 ZCKM6 ZCKM6H29 ZCKM6H7 ZCKM7 ZCKM7H29 ZCKM7H7 ZCKM8 |

Atsakomybės apribojimas: Šių dokumentų tikslas nėra nurodyti gaminių tinkamumą tam tikram naudojimui ar nustatyti jų patikimumą. Jie taip pat neatsižvelgia į patikimumo ar patikimumo nustatymo

ZCKM8H29
 ZCKM8H7
 ZCKM9
 ZCKM9H29
 ZCKMD31
 ZCKMD31H29
 ZCKMD31H7
 ZCKMD35
 ZCKMD35H29
 ZCKMD35H7
 ZCKMD37
 ZCKMD37H29
 ZCKMD37H7
 ZCKMD39
 ZCKMD39H29
 ZCKMD39H7

| | |
|----------------------------|--|
| Movement of operating head | Linear Rotary |
| Type of operator | Roller lever plunger spring return thermoplastic |
| Type of approach | Lateral approach 1 direction |

Complementary

| | |
|------------------|------------|
| Switch actuation | By 30° cam |
| Positive opening | With |
| Head material | Plastic |

Environment

| | |
|---------------------------------------|----------------------|
| Ambient air temperature for operation | -25...70 °C |
| Ambient air temperature for storage | -40...70 °C |
| Environmental characteristic | Standard environment |

Offer Sustainability

| | |
|----------------------------------|---|
| Sustainable offer status | Green Premium product |
| RoHS (date code: YYWW) | Compliant - since 1012 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity |
| REACH | Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold |
| Product end of life instructions | Need no specific recycling operations |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|