# **Product datasheet**

Specifications





# insulated double cable end medium size 0.75 mm<sup>2</sup> blue

AZ5DE007

#### Main

mann	
Range Of Product	Linergy
Product Or Component Type	Cable end
Cable End Size	Medium
Standards	NF C 63-023
Type Of Packing	Dispenser pack
Quantity Per Set	5 sets of 100
Cable Cross Section	0.75 mm²

#### Complementary

Cable End TypeTwin conductorAdditional InformationWithout marker tag holderColourBlueBezel MaterialHalogen-free plasticTube MaterialCopper conforming to ISO 1337Number Of Cables2Awg GaugeAWG 20Bezel SizeØ 2.8 x 5 mmTube Diameter2 mm	
Colour Blue   Bezel Material Halogen-free plastic   Tube Material Copper conforming to ISO 1337   Number Of Cables 2   Awg Gauge AWG 20   Bezel Size Ø 2.8 x 5 mm	
Bezel Material Halogen-free plastic   Tube Material Copper conforming to ISO 1337   Number Of Cables 2   Awg Gauge AWG 20   Bezel Size Ø 2.8 x 5 mm	
Tube Material Copper conforming to ISO 1337   Number Of Cables 2   Awg Gauge AWG 20   Bezel Size Ø 2.8 x 5 mm	
Number Of Cables 2   Awg Gauge AWG 20   Bezel Size Ø 2.8 x 5 mm	
Awg Gauge AWG 20   Bezel Size Ø 2.8 x 5 mm	
Bezel Size Ø 2.8 x 5 mm	
Tube Diameter 2 mm	
Length 15 mm	
Tube Length 8 mm	
Net Weight 0.13 kg	

#### Environment

Product Certifications	cCSAus
Ambient Air Temperature For Operation	-20105 °C

#### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.400 cm
Package 1 Width	0.400 cm

Package 1 Length	1.400 cm
Package 1 Weight	0.100 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	500
Package 2 Height	13.000 cm
Package 2 Width	7.000 cm
Package 2 Length	12.500 cm
Package 2 Weight	134.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	20000
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	6.214 kg

## **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

#### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Circularity Profile	No need of specific recycling operations
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Reach Regulation	REACh Declaration