

Product datasheet

Specifications



Full-flat switch with Ondicator, ZENcole, 16AX/20A, 1 gang, 2 way

E8431_2_SZ

Price : 3,622.87 NGN

Main

| | |
|---------------------------|---|
| Range | ZENcelo |
| Product or component type | Switch |
| Load type | Fluorescent lamp Resistive Inductive Incandescent lamp |
| Colour tint | Silver satin |

Complementary

| | |
|-------------------------|---|
| Device mounting | Flush Surface |
| Switch function | 2-way |
| Rated current | 20 A at 250 V AC 50 Hz 16 AX |
| Local signalling | Mechanical indicator, neon (amber) |
| Number of gangs | 1 gang |
| Material | Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: cover Polycarbonate: surround |
| Connections - terminals | Brass rod terminals |
| Width | 87 mm |
| Height | 87 mm |
| Depth | 31 mm |

Environment

| | |
|---------------------------------------|---|
| Ambient air temperature for operation | -5...35 °C |
| Relative humidity | 0...95 % |
| Environmental characteristic | No UV resistant |
| Operating altitude | 2000 m |
| Standards | IEC 60669-1 EN 60669-1 GB 16915.1 MS IEC 60669-1 SS 227-1 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3.5 cm |
| Package 1 Width | 8.7 cm |
| Package 1 Length | 8.7 cm |
| Package 1 Weight | 101.59 g |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 8 |
| Package 2 Height | 9.5 cm |
| Package 2 Width | 15 cm |
| Package 2 Length | 19 cm |
| Package 2 Weight | 812.72 g |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 80 |
| Package 3 Height | 21 cm |
| Package 3 Width | 32.5 cm |
| Package 3 Length | 50 cm |
| Package 3 Weight | 8127.2 g |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |

Recommended replacement(s)