
Product datasheet

Specifications



Main

Cabling Installation System	Post Trunking Pole
Product Or Component Type	Front cover

Complementary

e emprementar y	
Type Of Pole	Two-sided One-sided
Type Of Post	Two-sided One-sided
Colour Tint	Natural
Quantity Per Set	24 m
Trunking Material	Aluminium
Trunking Dimension	120 x 55 mm 185 x 55 mm 80 x 55 mm 155 x 55 mm 95 x 55 mm
Pole/Post Surface Finish	Anodized
Pole Fixing Mode	Free-standing Tension-mounted
Fixing Mode	Snap-fitted
Material	Aluminium anodized
Length	2000 mm
Height	71 mm
Width	13 mm
Market Segment	Small commercial Residential

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-2-1:2002 NF C 68-102
Ambient Air Temperature For Operation	-2560 °C
Ip Degree Of Protection	IP40

Packing Units

U	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	2
Package 1 Height	71 cm
Package 1 Width	13 cm
Package 1 Length	2000 cm
Package 1 Weight	678 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	24
Package 2 Height	5.2 cm
Package 2 Width	15.8 cm
Package 2 Length	220 cm
Package 2 Weight	8.533 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	1512
Package 3 Height	120 cm
Package 3 Width	59.9 cm
Package 3 Length	256 cm
Package 3 Weight	558.579 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations