

Product data sheet

Specifications



FRONT PLATE VIGI NSX.TOGGLE / CVS.ROTARY - 4P 630A HORIZONTAL WIDTH650 4MODULES

03644

⚠ Discontinued

⚠ Discontinued on: 18/09/2023

Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Type Of Front Plate	Cut-out

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Installed Device	ComPact: fixed NSX400 without earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX630 without earth leakage protection - control: toggle - horizontal installation EasyPact: fixed CVS400 without earth leakage protection - control: direct front rotary handle - horizontal installation EasyPact: fixed CVS630 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: plug-in NSX400 without earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX400 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX400 without earth leakage protection - control: motor mechanism - horizontal installation ComPact: plug-in NSX400 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: plug-in NSX400 without earth leakage protection - control: motor mechanism - horizontal installation ComPact: plug-in NSX630 without earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX630 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX630 without earth leakage protection - control: motor mechanism - horizontal installation ComPact: plug-in NSX630 without earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: plug-in NSX630 without earth leakage protection - control: motor mechanism - horizontal installation EasyPact: fixed CVS400 with earth leakage protection - control: direct front rotary handle - horizontal installation EasyPact: fixed CVS630 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX400 with earth leakage protection - control: toggle - horizontal installation ComPact: plug-in NSX400 with earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX400 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX400 with earth leakage protection - control: motor mechanism - horizontal installation ComPact: plug-in NSX400 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: plug-in NSX400 with earth leakage protection - control: motor mechanism - horizontal installation ComPact: fixed NSX630 with earth leakage protection - control: toggle - horizontal installation ComPact: plug-in NSX630 with earth leakage protection - control: toggle - horizontal installation ComPact: fixed NSX630 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: fixed NSX630 with earth leakage protection - control: motor mechanism - horizontal installation ComPact: plug-in NSX630 with earth leakage protection - control: direct front rotary handle - horizontal installation ComPact: plug-in NSX630 with earth leakage protection - control: motor mechanism - horizontal installation
------------------	--

Poles Description	1 x 4P: mounting plate support: CVS400 horizontal installation 1 x 4P: mounting plate support: CVS630 horizontal installation 1 x 4P: mounting plate support: NSX400 horizontal installation 1 x 4P: mounting plate support: NSX630 horizontal installation
-------------------	--

Operating Position	Horizontal
--------------------	------------

Complementary

Enclosure/Cubicle Description	Cubicle - width 650 mm depth 400 mm
Connection Position	Direct connection
Number Of Vertical Modules [50 Mm]	5
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA

Surface Finish	Smooth Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	250 mm
Net Weight	0.94 kg
Quantity Per Set	Set of 1
Functional Unit	650 mm 400 mm Prisma P cubicle EasyPact CVS400 without fixed direct front rotary handle horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle EasyPact CVS630 without fixed direct front rotary handle horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed toggle horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in toggle horizontal 4P 1 direct 4 650 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed direct front rotary handle horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX400 without fixed motor mechanism horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in direct front rotary handle horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX400 without plug-in motor mechanism horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed toggle horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in toggle horizontal 4P 1 direct 4 650 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed direct front rotary handle horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX630 without fixed motor mechanism horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in direct front rotary handle horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX630 without plug-in motor mechanism horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle EasyPact CVS400 with fixed direct front rotary handle horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle EasyPact CVS630 with fixed direct front rotary handle horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX400 with fixed toggle horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX400 with plug-in toggle horizontal 4P 1 direct 4 650 mm 400 mm Prisma P cubicle ComPact NSX400 with fixed direct front rotary handle horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX400 with fixed motor mechanism horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX400 with plug-in direct front rotary handle horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX400 with plug-in motor mechanism horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX630 with fixed toggle horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX630 with plug-in toggle horizontal 4P 1 direct 4 650 mm 400 mm Prisma P cubicle ComPact NSX630 with fixed direct front rotary handle horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX630 with fixed motor mechanism horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX630 with plug-in direct front rotary handle horizontal 4P 1 direct 5 650 mm 400 mm Prisma P cubicle ComPact NSX630 with plug-in motor mechanism horizontal 4P 1 direct 5

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.000 cm

Package 1 Width	26.000 cm
Package 1 Length	51.000 cm
Package 1 Weight	948.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	17.000 cm
Package 2 Width	27.000 cm
Package 2 Length	53.000 cm
Package 2 Weight	9.720 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	270
Package 3 Height	95.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	262.980 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information