
Product data sheet

Specifications





FR.PL.INS1600 4P

03714

Discontinued on: 18/09/2023



Main

Range	Prisma	
Range Of Product	Prisma P	
Product Or Component Type	Front plate	
Accessory / Separate Part Category	Installation accessory	
Range Compatibility	Prisma Prisma P cubicle	
Type Of Front Plate	Cut-out	
Installed Device	ComPact: fixed INS630b1600 - control: direct front rotary handle - vertical installation ComPact: fixed INV630b1600 - control: direct front rotary handle - vertical installation	
Poles Description	1 x 4P: mounting plate support: INS630b1600 vertical installation 1 x 4P: mounting plate support: INV630b1600 vertical installation	
Operating Position	Vertical	

Complementary

Enclosure/Cubicle Description	Cubicle - width 650 mm depth 400 mm
Connection Position	·
Connection Fosition	Front connection Rear connection
	Rear connection
Number Of Vertical Modules [50 Mm]	6
Standards	IEC 61439-1
	IEC 61439-2
Product Certifications	ASEFA
Material	Steel
Surface Finish	Matt
	Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	300 mm
Width	500 mm
Net Weight	0.92 kg
Quantity Per Set	Set of 1
Functional Unit	650 mm 400 mm Prisma P cubicle ComPact INS630b1600 fixed direct front rotary handle vertical 4P 1 front connection on adaptor 14 650 mm 400 mm Prisma P cubicle ComPact INV630b1600 fixed direct front rotary handle vertical 4P 1 front connection on adaptor 14



Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.3 cm
Package 1 Width	30.5 cm
Package 1 Length	50.0 cm
Package 1 Weight	930.0 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	16
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	15.2 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	80
Package 3 Height	78.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	82.0 kg

26/04/2024



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information