Product datasheet

Specifications





socket RUZ- separate contact -12 A - < 250 V - connector

RUZSF3M

Main

Range Of Product	Harmony Electromechanical Relays
Device Short Name	RUZ
Product Or Component Type	Socket
Product Compatibility	Plug-in relay RUM with 2 C/O contact Plug-in relay RUM with 3 C/O contact
Contacts Type And Composition	3 C/O
[Ith] Conventional Free Air Thermal Current	16 A
[Ue] Rated Operational Voltage	< 250 V

Complementary

Shape Of Pin	Flat	
Contact Terminal Arrangement	Separate	
Connections - Terminals	Connector, 1 x 0.251 x 2.5 mm² (AWG 22AWG 14) flexible with cable end Connector, 2 x 0.252 x 1 mm² (AWG 22AWG 17) flexible with cable end Connector, 1 x 0.51 x 2.5 mm² (AWG 20AWG 14) solid without cable end Connector, 2 x 0.52 x 1.5 mm² (AWG 20AWG 16) solid without cable end	
Tightening Torque	< 1 N.m for M3.5 screw(s)	
Fixing Mode	By screw (panel) Clip-on (35 mm symmetrical DIN rail)	
[Uimp] Rated Impulse Withstand Voltage	4 kV	
Overvoltage Category	III	
Pollution Degree	3	
Sale Per Indivisible Quantity	10	
Width	36 mm	
Net Weight	0.095 kg	

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529	
Standards	IEC 61984	
Product Certifications	CSA UL	
Marking	CE	
Ambient Air Temperature For Storage	-4085 °C	
Ambient Air Temperature For Operation	-4055 °C	

19 Apr 2024 Life Is On Schneider

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	9.2 cm
Package 1 Length	6.3 cm
Package 1 Weight	103.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	10.4 cm
Package 2 Width	11.2 cm
Package 2 Length	18.7 cm
Package 2 Weight	1.05 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	80
Package 3 Height	28.5 cm
Package 3 Width	29.9 cm
Package 3 Length	39.8 cm
Package 3 Weight	8.4 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations

RUZSF3M

Dimensions Drawings

Dimensions




- (1) Relays
 (2) Protection module
- (3) Maintaining clamp
- (4) 2 bus jumpers

Product datasheet

RUZSF3M

Connections and Schema

Wiring Diagram




Symbols shown in blue correspond to Nema marking.

RUZSF3M

Bus Jumpers Mounting on Sockets with Separate Contacts

Example of RUZS2 bus jumper mounting on sockets (view from below)



- (1) 2 bus jumpers (polarity A2)(2) 2 bus jumpers (polarity A1)

19 Apr 2024