# **Product data sheet**





## LINERGY BS 4P MULTISTAGE **BB 250A 52HOLES**

04053

! Discontinued on: 23/03/2023

① Discontinued

#### Main

Range	Linergy	
Range Of Product	Linergy	
Product Or Component Type	Multi-stage distribution block	
Product Name	Linergy BS	
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P enclosure	
Product Compatibility	Spacial enclosures	
Ip Degree Of Protection	IPxx B	

### Complementary

Mounting Support	Plain backplate
	Prisma upright
Mounting Mode	Horizontal
	Vertical
Poles Description	4P
[Ue] Rated Operational Voltage	440 V AC
[Ui] Rated Insulation Voltage	750 V AC
[Uimp] Rated Impulse Withstand Voltage	8 kV
[le] Rated Operational Current	250 A
[In] Rated Current	250 A at 40 °C
[Icw] Rated Short-Time Withstand Current	13 kA for 1 s
[lpk] Rated Peak Withstand Current	30 kA
I <sup>2</sup> T On Activation	169000000 A².s
Busbar Cross Section	20 x 5 mm
Connections - Terminals	Supply: crimped lug50 mm²
	Supply: flexible bars, 20 x 3 mm
	Distribution: M6 holes (phase) , 13 x 150 mm <sup>2</sup>
Height	235 mm
Width	470 mm
Depth	115 mm
Net Weight	3.2 kg

#### **Environment**

Standards	IEC 61439-2 EN/IEC 61439-1
Product Certifications	ASEFA

### **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.5 cm
Package 1 Width	26 cm
Package 1 Length	55 cm
Package 1 Weight	3.11 kg

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>②</b>	Toxic Heavy Metal Free	
<b>9</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins