Product data sheet





LINERGY BS 4P MULTISTAGE **BB 630A 52HOLES**

04055

! Discontinued on: 23/03/2023

① Discontinued

Main

Range	Linergy
Range Of Product	Linergy
Product Or Component Type	Multi-stage distribution block
Product Name	Linergy BS
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P enclosure
Product Compatibility	Spacial enclosures
Ip Degree Of Protection	IPxx B

Complementary

Mounting Support	Slotted backplate
	Prisma upright
	Plain backplate
Mounting Mode	Vertical
	Horizontal
Poles Description	4P
[Ue] Rated Operational Voltage	440 V AC
[Ui] Rated Insulation Voltage	750 V AC
[Uimp] Rated Impulse Withstand Voltage	8 kV
[le] Rated Operational Current	630 A
[In] Rated Current	630 A at 40 °C
[Icw] Rated Short-Time Withstand Current	25 kA for 1 s
[lpk] Rated Peak Withstand Current	40 kA
I ² T On Activation	625000000 A².s
Busbar Cross Section	32 x 8 mm
Connections - Terminals	Supply: crimped lug50 mm²
	Supply: flexible bars, 32 x 8 mm
	Distribution: M6 holes (phase) , 13 x 150 mm²
Height	235 mm
Width	470 mm
Depth	115 mm
Net Weight	5.6 kg

Environment

Standards	IEC 61439-2 EN/IEC 61439-1	
Product Certifications	ASEFA	

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.5 cm
Package 1 Width	26 cm
Package 1 Length	55 cm
Package 1 Weight	5.61 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins