

Product datasheet

Specifications



modular buzzer iRO - 230 V
50/60Hz - 70 dB

A9A15322

Price: 24,068.18 NGN

Main

Range Of Product	Acti9
Product Name	Acti9 iRO
Product Or Component Type	Buzzer
Device Short Name	iRO

Complementary

[Us] Rated Supply Voltage	230 V AC at 50/60 Hz
Power Consumption In Va	5 VA
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	2
Height	81 mm
Width	18 mm
Depth	72 mm
Net Weight	64 g
Colour	White
Auxiliary Connection Terminal	Tunnel type terminalsrigid 4 mm² Tunnel type terminalsflexible 4 mm² Tunnel type terminalsflexible with ferrule 4 mm²
Wire Stripping Length	12 mm for bottom connection
Tightening Torque	1.3 N.m

Environment

Noise Level	70 dB
Type Of Sound	Buzzer
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Ambient Air Temperature For Operation	-10...40 °C
Ambient Air Temperature For Storage	-25...60 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	1.8 cm
Package 1 Width	6.6 cm
Package 1 Length	8.2 cm
Package 1 Weight	55.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.3 cm
Package 2 Width	10.0 cm
Package 2 Length	22.8 cm
Package 2 Weight	715.0 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	144
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	9.115 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability




Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
 Halogen Free Product	
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins