Product data sheet

Specifications





RIO head-end adaptor module Modicon Quantum - 2 connectors with redundant cable

140CRP93200C

- Discontinued on: 31/12/2023
- (!) To be end-of-service on: 31/12/2029

Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	RIO head-end adaptor module

Complementary

complementary	
Product Compatibility	Symax (any mix) Quantum 200/500/800 series
Maximum Drops/Network	31
I/O Words/Drop	64 1/64 O
Type Of Cable	75 Ohm coaxial cable
Transmission Rate	1544 Mbit/s
Dynamic Range	35 dB
Isolation Voltage	500 V DC coaxial center and ground
Electrical Connection	2 female connectors F, elbowed with redundant cable
Diagnostics Startup	Power up LAN controller check Memory check
Power Dissipation In W	3 W 2 channels
Marking	CE
Bus Current Requirement	750 mA 2 channels
Module Format	Standard

Environment

Protective Treatment	Conformal coating Humiseal 1A33
Product Certifications	FM Class 1 Division 2
Standards	UL 508 CUL CSA C22.2 No 142
Resistance To Electrostatic Discharge	4 kV contact conforming to IEC 801-2 8 kV on air conforming to IEC 801-2
Resistance To Electromagnetic Fields	10 V/m 801000 MHz conforming to IEC 801-3
Ambient Air Temperature For Operation	060 °C
Ambient Air Temperature For Storage	-4085 °C

Relative Humidity	95 % without condensation
Operating Altitude	<= 5000 m

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	16.5 cm
Package 1 Length	31.0 cm
Package 1 Weight	548.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	7
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.836 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Reach Free Of Svhc

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards


Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Product data sheet

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks



- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots