## **Product datasheet**

Specifications





# Switched Socket, Vivace, 15A, 250V, 1 gang, aluminium silver

KB15\_15\_AS

Price: 11,284.09 NGN

#### Main

Range	Vivace
Product Or Component Type	Switched socket
Device Short Name	KB15
Device Application	Power supply
Device Presentation	Complete product
Switch Application	On/off switching
Main Colour Tint	Aluminium silver
Colour Tint	Wall: aluminium silver

### Complementary

Outlet Poles Configuration	2P + E
Number Of Gangs	1 gang
Colour Tint	Aluminium silver
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base
Projecting Depth	8 mm
Device Mounting	Flush
Mounting Support	Wall mounted
Fixing Mode	By screw M3.5
Fixing Center	60.3 mm
Embedding Depth	28 mm
Rated Current	15 A at 250 V AC, resistive
Network Frequency	50/60 Hz
Contacts Material	Brass and phosphor bronze
Connections - Terminals	Pillar terminal
Terminal Identifier	N Earth L
Tightening Torque	0.4 N.m
Clamping Connection Capacity	2 x 4 mm <sup>2</sup> 3 x 2.5 mm <sup>2</sup>
Width	86 mm
Height	86 mm

Depth

#### Environment

Standards	MS 589 BS 1362-2 SS 145
Ambient Air Temperature For Operation	-540 °C
Ambient Air Temperature For Storage	-560 °C
Relative Humidity	095 %
Operating Altitude	<= 2000 m
Environmental Characteristic	Indoor use
Ip Degree Of Protection	IP20

## **Packing Units**

V	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.6 cm
Package 1 Width	3.2 cm
Package 1 Length	8.6 cm
Package 1 Weight	118 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	1.25 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	100
Package 3 Height	31.5 cm
Package 3 Width	50 cm
Package 3 Length	50 cm
Package 3 Weight	12054 g

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free

Mercury Free

Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations