Product datasheet

Specifications





Vivace 5A 250V 1Gang Switched socket, Aluminium silver

KB15_5_AS

! Discontinued on: 30 Jun 2023

① Discontinued

Main

Range	Vivace	
Product Or Component Type	Switched socket	
Device Short Name	KB15	
Device Application	Power supply	
Device Presentation	Complete product	
Main Colour Tint	Aluminium silver	
Colour Tint	Aluminium silver	

Complementary

Complementary		
Outlet Poles Configuration	2P + E	
Number Of Gangs	1 gang	
Colour Tint	Aluminium silver	
Material	Polycarbonate: grid plate Polycarbonate: surround Polycarbonate: base	
Projecting Depth	8 mm	
Device Mounting	Flush	
Mounting Support	Wall mounted	
Fixing Mode	By screw M3.5	
Fixing Center	60.3 mm	
Embedding Depth	35 mm	
Rated Current	5 A at 250 V AC, resistive 5 A at 250 V AC, inductive	
Network Frequency	50 Hz	
Contacts Material	Brass and phosphor bronze	
Connections - Terminals	Pillar terminal	
Terminal Identifier	N Earth L	
Tightening Torque	0.4 N.m	
Clamping Connection Capacity	<= 1.5 mm²	
Width	86 mm	
Height	86 mm	

Depth 35 mm

Environment

Standards	BS 546
Ambient Air Temperature For Operation	-540 °C
Relative Humidity	095 %
Environmental Characteristic	Indoor use

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.7 cm
Package 1 Width	8.6 cm
Package 1 Length	8.6 cm
Package 1 Weight	86 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	9.5 cm
Package 2 Width	15 cm
Package 2 Length	19 cm
Package 2 Weight	760 g
Unit Type Of Package 3	CAR
Number Of Units In Package 3	80
Package 3 Height	21 cm
Package 3 Width	31.5 cm
Package 3 Length	50 cm
Package 3 Weight	7210 g



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations