Product datasheet

Specification





MN undervoltage release, ComPacT NSX, rated voltage 110/130 VAC 50/60 Hz, screwless spring terminal connections

LV429406

Price: 83,325.89 NGN

Main

Range	ComPacT
Range Of Product	ComPact NSX100250
	ComPacT NSX100250 new generation
	ComPact NSX400630
	ComPacT NSX400630 new generation
	ComPact NSX100250 DC
	ComPacT NSX100250 DC new generation
	ComPact NSX100250 DC PV
	ComPacT NSX100250 DC PV new generation
	ComPact NSX400630 DC
	ComPacT NSX400630 DC new generation
	ComPact NSX400630 DC PV
	ComPacT NSX400630 DC PV new generation
Device Short Name	MN
Product Or Component Type	Voltage release
Device Application	Control
Voltage Release Type	Opening coil
	Undervoltage release
[Uc] Control Circuit Voltage	110130 V AC 50/60 Hz
Range Compatibility	ComPacT new generation ComPacT NSX new generation
	ComPacT new generation ComPacT NSX DC new generation
	ComPact ComPact NSX
	ComPact ComPact NSX DC
	EasyPact EasyPact CVS
	PowerPact PowerPact Multistandard

Complementary

Operating Threshold	0.350.7 x Un opening 0.85 x Un closing
Response Time	50 ms
Supply Holding Power	5 VA
Supply Inrush Power	10 VA
Auxiliary Connection Terminal	Spring 0.51.5 mm² (AWG 20AWG 16)
Wire Stripping Length	7 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	6.3 cm

Package 1 Length	8 cm
Package 1 Weight	130 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9 cm
Package 2 Width	15 cm
Package 2 Length	23.5 cm
Package 2 Weight	1.4 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	60
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	8.84 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >


Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations