
Product data sheet

Specifications



Microperforated mounting plate H1000xW800 w/ holes diam 3,6mm on 12,5mm pitch

NSYMF108

Main

Range	Spacial	
Accessory / Separate Part Category	Mounting accessory	
Product Or Component Type	Mounting plate	
Device Application	Multi-purpose	
Enclosure Nominal Dimensions	- H: 800 mm W: 1000 mm - H: 1000 mm W: 800 mm	
Mounting Location	Step slide Direct fixing on backstuds	
Mounting Plate Description	Microperforated	
Range Compatibility	Spacial Spacial S3D Spacial Spacial CRN Spacial Spacial S3X	
Quantity Per Set	Set of 1	
Material	Galvanised steel	

Complementary

Fixing Mode	Screwed on backstuds - screw type M8 By fixing element	
Permanent Permissible Load	150 kg	
Height	965 mm	
Width	750 mm	
Depth	125 mm	
Thickness	2.5 mm	
Net Weight	12.88 kg	
Variant Particularity	Installation in enclosures with inverted dimensions	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.3 cm
Package 1 Width	75.5 cm
Package 1 Length	96.5 cm
Package 1 Weight	13.27 kg
Unit Type Of Package 2	PAM

Number Of Units In Package 2	40	
Package 2 Height	32.0 cm	
Package 2 Width	100.0 cm	
Package 2 Length	120.0 cm	
Package 2 Weight	554.0 kg	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations