
Product data sheet

Specifications





(!) Discontinued

LINERGY LGYE PROFILE 1600A LENGTH 2000MM

04564

- ! Discontinued on: Nov 10, 2021
- ! End-of-service on: Jan 15, 2022

Main

Range	Linergy
Range Of Product	Linergy
Product Or Component Type	Profile busbar
Product Name	Linergy LGYE
Range Compatibility	Prisma Prisma P enclosure
Busbar Description	Linergy
Quantity Per Set	Set of 1

Complementary

Installation Direction	Horizontal, operating position: top Horizontal, operating position: bottom
Installation Description	Cubicle - width 650 mm Cubicle - width 650 + 150 mm Cubicle duct - width 300 mm Cubicle duct - width 400 mm
[Ui] Rated Insulation Voltage	1000 V
[Uimp] Rated Impulse Withstand Voltage	12 kV (degree of pollution: 3)
[le] Rated Operational Current	1600 A
[Icw] Rated Short-Time Withstand Current	85 kA (1 s) for 3 supports (horizontal position) 50 kA (1 s) for 2 supports (horizontal position)
Permissible Current	1650 A at 35 °C: <= IP31 1480 A at 35 °C: > IP31
Length	2000 mm
Height	150 mm
Width	60 mm
Depth	23 mm
Net Weight	5.16 kg
Type Of Busbar Connection	Single t-slot
Connection Pitch	Free connection position
Support Thickness	5 mm

Environment

Chandanda		
Standards	IEC 61439-1	
	IEC 61439-2	

List Price displayed is VAT EXCLUSIVE.

Apr 23, 2024 Life Is On Schneider 1

Product Certifications ASEFA

Packing Units

Number Of Units In Package 1



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
Ø	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive

	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Compliant