



ADDITIONAL BLK 2X35² 4P/ **LINERGY DP 250A**

04156

Main

Range	Linergy
Range Of Product	Linergy
Product Or Component Type	Distribution block
Product Name	Linergy DP
Range Compatibility	Prisma Prisma P enclosure Prisma Prisma G enclosure Linergy Linergy DP distribution block
Accessory / Separate Part Category	Current distribution accessory
Ip Degree Of Protection	IPxx B

Complementary

Mounting Support	Mounting plate
Installed Device	EasyPact: CVS100250 ComPact: NSX100250 ComPact: INV100250 ComPact: INS100160 ComPact: INS250
Poles Description	4P
[Ue] Rated Operational Voltage	690 V AC
[Ui] Rated Insulation Voltage	750 V AC
[Uimp] Rated Impulse Withstand Voltage	8 kV
[le] Rated Operational Current	250 A at 40 °C
[Icw] Rated Short-Time Withstand Current	8.5 kA for 1 s
[lpk] Rated Peak Withstand Current	30 kA
Connections - Terminals	Supply: direct connection120 mm ² Distribution: screw terminal, 2 x 35 mm ²
Net Weight	0.3 kg

Environment

Pollution Degree	3
Overvoltage Category	III
Resistance To Incandescent Wire	960 °C conforming to IEC 60695-2-11
Standards	IEC 60947-7-1

IEC 61439-1, inside Prisma IEC 61439-2, inside Prisma

Product Certifications	ASEFA
Ambient Air Temperature For Operation	-2555 °C
Packing Units	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6 cm
Package 1 Width	8 cm
Package 1 Length	14.5 cm

300 g

Package 1 Weight



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
9	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins