



auxiliary contact - 1 OC + 1 SD/OC - 380..415 V - 6 A

26929

! Discontinued on: Sep 30, 2021 AD

(!) To be discontinued

Main

Range Of Product	Multi9		
Product Or Component Type	Double OC or fault contact		
Device Short Name	OF and OF or OF and SD		
Signal Contacts Composition	2 C/O		
[In] Rated Current	DC-12 1 A at 130 V, DC DC-12 2 A at 48 V, DC DC-12 6 A at 24 V, DC AC-12 3 A at 415 V, AC 50/60 Hz AC-12 6 A at 240 V, AC 50/60 Hz		
9 Mm Pitches	1		

Complementary

Mounting Mode	Fixed		
Mounting Support	DIN rail		
Height	84 mm		
Width	9 mm		
Depth	73 mm		
Connections - Terminals	Clamp terminal2 cable(s) 1.5 mm² - flexible Clamp terminal2 cable(s) 1.5 mm² - rigid Clamp terminal1 cable(s) 0.52.5 mm² - flexible Clamp terminal1 cable(s) 0.52.5 mm² - rigid		
Wire Stripping Length	9 mm		
Tightening Torque	1 N.m		

Environment

Standards	EN/IEC 60947-5-1	
Product Certifications	LCIE	
	ASEFA	
	KEMA	
	ASTA	
Ip Degree Of Protection	IP20 conforming to EN/IEC 60947-5-1	
Pollution Degree	3 conforming to EN/IEC 60947-5-1	
Tropicalisation	2 conforming to EN/IEC 60947-5-1	
Relative Humidity	95 % at 55 °C	
Ambient Air Temperature For Operation	-2550 °C	

Ambient Air Temperature For	-4085 °C
Storage	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	8 cm
Package 1 Length	9 cm
Package 1 Weight	46 g

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	Compliant EU RoHS Declaration	
Eu Rohs Directive		
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	End of Life Information	