Product data sheet

Specification





control unit Micrologic 2.0 A, for Masterpact NT/NW, LI protections

33071

① Discontinued

Main

Control unit
MicroLogic 2.0 A
Electronic
MasterPact NT
MasterPact NW
Compact NS
Masterpact MT
Distribution
4P
3P
4t
3t
3t + N/2
Basic protection
for overload protection (long time)
for instantaneous short-circuit protection
630 A at 50 °C
800 A at 50 °C
1000 A at 50 °C
1250 A at 50 °C
1600 A at 50 °C
2000 A at 50 °C
2500 A at 50 °C
3200 A at 50 °C
4000 A at 50 °C
5000 A at 50 °C
6300 A at 50 °C
AC
50/60 Hz
Fixed

Complementary

Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable 9 settings
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.41 x ln
Long-Time Protection Delay Adjustment Type Tr	Adjustable 9 settings
[Tr] Long-Time Protection Delay Adjustment Range	0.716.6 s at 7.2 x lr 0.724 s at 6 x lr 12.5600 s at 1.5 x lr
Thermal Memory	20 mn

List Price displayed is VAT EXCLUSIVE.

Instantaneous Protection Pick-Up Adjustment Type Ii	Adjustable 9 settings
[li] Instantaneous Protection Pick- Up Adjustment Range	1.510 x lr
Earth-Leakage Protection	Without
Zone Selective Interlocking Zsi	Without
Local Signalling	3 LEDs (red) for electrical fault 1 LED (red) for internal error
Display Type	Digital display
Type Of Measurement	Ammeter
Communication Of Data	Measurement readout Protection and alarm settings

Environment

Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.8 cm
Package 1 Width	8 cm
Package 1 Length	21.5 cm
Package 1 Weight	247 g

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Mercury Free	
	Rohs Exemption Information	Yes
	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information