

Product data sheet

Specifications



carriage auxiliary switch NO/NC 6 A
- 240 V - for Masterpact NT/NW
NS630b..1600

33170

Main

Device Short Name	carriage switch
Product Or Component Type	Auxiliary contact
Device Application	Monitoring
Range Compatibility	Masterpact MasterPact NT Masterpact MasterPact NW Masterpact MasterPact NW DC ComPact ComPact NS630b...1600
Signal Contacts Composition	1 NO/NC

Complementary

Auxiliary Contacts Type	Standard
Auxiliary Contacts Operation	Connected position Test position Disconnected position
Mounting Mode	Drawout
[Ie] Rated Operational Current	AC-12: 6 A at 690 V AC 50/60 Hz AC-12: 8 A at 240 V AC 50/60 Hz AC-12: 8 A at 380 V AC 50/60 Hz AC-12: 8 A at 480 V AC 50/60 Hz DC-12: 0.3 A at 250 V DC DC-12: 0.8 A at 125 V DC DC-12: 2.5 A at 24/48 V DC
Minimum Load	100 mA at 24 V
Accessory / Separate Part Category	Spare part for MasterPact NT Spare part for MasterPact NW Spare part for MasterPact NW DC Spare part for ComPact NS630b...1600

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.0 cm
Package 1 Width	5.0 cm
Package 1 Length	5.0 cm
Package 1 Weight	18.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	100
Package 2 Height	7.0 cm

List Price displayed is VAT EXCLUSIVE.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	21.0 cm
Package 2 Length	35.0 cm
Package 2 Weight	1.8 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	600
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	11.25 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)