

Lista sa podacima o proizvodima

Specifikacije



Mureva Wander utikač - ravni - 16 A - 2P - 20...25 V AC - IP44

82301

Cena* bez PDV-a: 1.033,00 RSD

Osnovne informacije

Grupa Proizvoda	Mureva
Tip Proizvoda Ili Komponente	Wander utikač
Kratko Ime Uređaja	Mureva plug
Kategorija Priključnice I Utikača	Veoma nizak napon
Broj Polova	2P
Tip Mreže	AC
Standard Utičnice	Industrijski

Dopunske informacije

Kategorija Priključnice I Utikača	Ravna
[In] Nazivna Struja	16 A
[Ue] Nazivni Napon	20...25 V
Mrežna Frekvencija	50/60 Hz
Materijal Utikača, Utičnice	Kućište: samogasivi konstruisan polimer
Materijal Kontakta	Pinovi: poniklovan mesing
Povezivanje - Priključci	Neodvojivi zavrtnji
Poprečni Presek Kabla	4...10 mm ²
Spoljašnji Prečnik Kabla	6...23 mm
Kablovski Uvod	Kablovska uvodnica
Tip Navoja	Pg 21
Masa Proizvoda	0,141 kg
Visina	158 mm
Širina	57,5 mm
Dubina	57,5 mm
Boja	Siva (RAL 7035)
Boja Poklopca	Ljubičasta

Okruženje

Standardi	IEC 60309-1 IEC 60309-2
Ip Stepen Zaštite	IP44 u skladu sa IEC 60529

Ik Stepen Zaštite IK08 conforming to EN 62262
Sve cene koje su navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

Otpornost Na Vatru	850 °C u skladu sa IEC 60695-2-11
Relativna Vlažnost	50 % pri 40 °C 70 % pri 30 °C 90 % pri 20 °C
Nadmorska Visina Za Rad	2000 m
Temperatura Okoline Za Rad	35 °C 86400 s) -25...40 °C

Pakovanje

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6,0 cm
Package 1 Width	6,0 cm
Package 1 Length	15,9 cm
Package 1 Weight	131,0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9,0 cm
Package 2 Width	26,8 cm
Package 2 Length	27,0 cm
Package 2 Weight	1,434 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	40
Package 3 Height	30,0 cm
Package 3 Width	30,0 cm
Package 3 Length	40,0 cm
Package 3 Weight	6,224 kg

Ugovorna garancija

Garancija	18 months
-----------	-----------

Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO₂ proizvodima.

Vodič za procenu održivosti proizvoda je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)



Prozirnost



RoHS/REACH

Performanse dobrobiti



Informacije O Rohs Izuzecima

Da

Sertifikacija i standardi

Propis Reach	REACH deklaracija
Eu Rohs Direktiva	У складу са изузецима
Rohs Regulativa Za Kinu	RoHS deklaracija za Kinu Proizvod je izvan RoHS okvira za Kinu. Informativna deklaracija supstanci.
Izjava O Zaštiti Okoliša	Profil ekološke prihvatljivosti proizvoda
Profil Cirkularnosti	Nema potrebe za namenskim operacijama recikliranja