

Lista sa podacima o proizvodima

Specifikacije



podnaponski okidač - iMN - zaštitna jedinica - 115 VAC

A9A26959

Cena* bez PDV-a: 11.082,00 RSD

Osnovne informacije

Grupa Proizvoda	Acti 9
Tip Proizvoda Ili Komponente	Podnaponski okidač
Kratko Ime Uređaja	iMN
Napon Upravljačkog Kola	115 V AC 400 Hz
Tip Upravljanja	Standardni
9 Mm Redovi	2

Dopunske informacije

Kompatibilnost Grupe Proizvoda	Acti 9 Acti 9 iC65 Acti 9 Acti 9 ARA Acti 9 Acti 9 iDPN Vigi Acti 9 Acti 9 iID Acti 9 Acti 9 iSW-NA Acti 9 Acti 9 RCA Acti 9 Acti 9 iDPN (kineska verzija) Acti 9 Acti 9 iC60 prekidač sa dvostrukim priključkom Acti 9 Acti 9 iC40
Lokalna Signalizacija	Indikator akcije
Način Montiranja	Sistemom na klik
Nosači Za Montažu	DIN šina
Razvodni Blok Češljaste Sabirnice	Top and bottom: DA
Širina	18 mm
Boja	Bela
Povezivanje - Priključci	Vijčani priključak - 1 kabl(ovi) 7 mm ² - kruti Vijčani priključak - 2 kabl(ovi) 2,6 mm ² - kruti Vijčani priključak - 1 kabl(ovi) 5 mm ² - fleksibilni Vijčani priključak - 2 kabl(ovi) 2,6 mm ² - fleksibilni sa
Moment Pritezanja	1 N.m

Okruženje

Standardi	EN/IEC 60947-5-1
Tropikalizacija	2 u skladu sa EN/IEC 60947-5-1
Relativna Vlažnost	95 % pri 55 °C
Temperatura Okoline Za Rad Uređaja	-35...70 °C
Temperatura Okoline Za Skladištenje	-40...85 °C

Pakovanje

Sve cene koje su navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2,800 cm
Package 1 Width	8,000 cm
Package 1 Length	9,300 cm
Package 1 Weight	78,000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	8,800 cm
Package 2 Width	10,000 cm
Package 2 Length	26,600 cm
Package 2 Weight	679,000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	72
Package 3 Height	30,000 cm
Package 3 Width	30,000 cm
Package 3 Length	40,000 cm
Package 3 Weight	6,604 kg

Ugovorna garancija

Garancija	18 meseci
-----------	-----------

Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO₂ proizvodima.

Vodič za procenu održivosti proizvoda je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)



Prozirnost



RoHS/REACH

Performanse dobrobiti

✓ Bez Žive	
✓ Informacije O Rohs Izuzecima	Da

Sertifikacija i standardi

Propis Reach	REACH deklaracija
Eu Rohs Direktiva	У складу са изузецима
Rohs Regulativa Za Kinu	RoHS deklaracija za Kinu Proizvod je izvan RoHS okvira za Kinu. Informativna deklaracija supstanci.
Izjava O Zaštiti Okoliša	Profil ekološke prihvatljivosti proizvoda
Weee	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Profil Cirkularnosti	Informacije o kraju radnog veka