


Lista sa podacima o proizvodima

Specifikacije



Asfora - serijski prekidač, vijčani priključak, bez rama, bronza

EPH0300369

Obustavljeno: 30. 6. 2023.

Cena* bez PDV-a: 372,00 RSD

Nije u prodaji

Osnovne informacije

Serija	Asfora
Tip Proizvoda Ili Komponente	Prekidač
Prezentacija Uređaja	Mehanizam sa montažnim ramom
Broj Prekidača	2
Funkcija Prekidača	Jednopolni izborni
Tip Opterećenja	Opterećenje za štedljive svetiljke sa balastom: 100 W
Nijansa Boje	Bronzana
Tip Pakovanja	Pakovanje u kesicama

Dopunske informacije

Montaža Uređaja	Ugradno
Opseg Snage	2300 W
Nazivna Struja	10 AX pri 250 V AC
Broj Kablova	2 kabl(ovi) 2,5 mm ²
Krutost Kabla	Fleksibilni Krući Jednožični višezični
Dužina Ogoljenog Dela Žice	13,0 mm
Materijal	ABS (akrilonitril-butadien-stiren)
Završna Obrada	Ofarban
Provodni Materijal	Bakar
Način Fiksiranja	Zavrtnji ili kukice51...70 mm
Povezivanje - Priključci	Vijčani priključci
Širina	71 mm
Visina	71 mm
Dubina	43,0 mm
Projektovana Dubina	15 mm
Masa Proizvoda	0,0652 kg

Okruženje

Standardi	IEC 60669-1
-----------	-------------

Sve cene koje su navedene u ovom cenovniku su informativne i neobavezujuće, bez PDV-a, isključivo u odnosu na ovlašćene distributere kompanije Schneider Electric. Svi prikazi, opisi i tehničke specifikacije i podaci u ovom cenovniku su podložni promenama od strane kompanije Schneider Electric bez prethodne najave.

Odricanje odgovornosti: Ova dokumentacija nije namenjena kao zamena i ne treba je koristiti za utvrđivanje podobnosti ili pouzdanosti ovih proizvoda za određene namene

Sertifikacija Proizvoda	VDE
Oznake Kvaliteta	CE
Ip Stepen Zaštite	IP20
Temperatura Okoline Za Rad Uređaja	-5...40 °C

Pakovanje

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4,000 cm
Package 1 Width	7,000 cm
Package 1 Length	7,000 cm
Package 1 Weight	66,300 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9,500 cm
Package 2 Width	18,500 cm
Package 2 Length	27,500 cm
Package 2 Weight	740,000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	120
Package 3 Height	30,000 cm
Package 3 Width	40,000 cm
Package 3 Length	60,000 cm
Package 3 Weight	9,524 kg

Održivost

Oznaka **Green Premium™** je posvećenost kompanije Schneider Electric isporuci proizvoda sa ekološkim performansama najboljim u klasi. Green Premium obećava usaglašenost sa najnovijim propisima, transparentnost u pogledu uticaja na životnu sredinu, kao i sa cirkularnim i niskonaponskim CO₂ proizvodima.

Vodič za procenu održivosti proizvoda je bela knjiga koja razjašnjava globalne standarde za oznaku ekološke prihvatljivosti i način tumačenja ekoloških izjava.

[Saznajte više o oznaci Green Premium >](#)

[Vodič za procenu održivosti proizvoda >](#)



Prozirnost



RoHS/REACH

Performanse dobrobiti



Informacije O Rohs Izuzecima

Da

Sertifikacija i standardi

Propis Reach	REACH deklaracija
Eu Rohs Direktiva	Usaglašeno EU RoHS deklaracija
Rohs Regulativa Za Kinu	RoHS deklaracija za Kinu Proaktivna RoHS deklaracija za Kinu (izvan RoHS pravnog okvira za Kinu)
Izjava O Zaštiti Okoliša	Profil ekološke prihvatljivosti proizvoda
Weee	Ovaj proizvod je na tržištima Evropske unije neophodno odložiti u skladu sa specifičnim smernicama za prikupljanje otpada i nikako ne sme da dospe u kontejnere za otpatke.
Profil Cirkularnosti	Nema potrebe za namenskim operacijama recikliranja