Product datasheet





Plug outlet, Linergy HK, 3P, 32A, 2 points, 4 mm², cable length 1000mm

AK5PC33L

Main

Range	Linergy	
Product Name	нк	
Product Or Component Type	Plug outlet	
Poles Description	3P	
[Ith] Conventional Free Air Thermal Current	32 A	
I ² T On Activation	200000 A².s	
Number Of Points	2	
Number Of Cables	3 cable(s) 4 mm ²	
Cable Length	1 m	
Quantity Per Set	Set of 6	

Complementary

[Ui] Rated Insulation Voltage	600 V conforming to CSA 600 V conforming to UL 690 V conforming to IEC 60439-1	
Peak Current	25 kA	
Width	36 mm	
Height	46 mm	
Depth	38 mm	

Environment

Standards	IEC 60439
Product Certifications	UL DNV LROS (Lloyds register of shipping)
	CSA

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.700 cm
Package 1 Width	23.500 cm
Package 1 Length	23.400 cm
Package 1 Weight	150.000 g

Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	8.700 cm
Package 2 Width	23.500 cm
Package 2 Length	23.400 cm
Package 2 Weight	990.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	54
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	9.800 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations