

Product datasheet

Specifications



Galaxy VM UPS Modular Battery Cabinet wide up to 12 strings

GVMMODBCW

Overview

Presentation	Wide modular battery cabinet with up to a 12 string modular battery capacity. To be used with GVMMBTU battery string. Batteries are not included in the SKU and must be purchased separately.
Lead Time	Usually Ships within 2 Weeks

Main

Main Input Voltage	480 V 3 phases
Battery Type	VRLA
Provided Equipment	Installation guide

Batteries & Runtime

Battery Location	Battery cabinet
Number Of Battery Free Slots	12
Number Of Battery Filled Slots	0
Device Mounting	Enclosed battery cabinet
Battery Voltage	480 V

Physical

Colour	White
Height	197 cm
Width	70 cm
Depth	85.4 cm
Net Weight	210 kg

Input

Network Frequency	40...70 Hz
-------------------	------------

Conformance

Standards	EN/IEC 62040-3 FCC part 15 class A OSHPD UL 1778
-----------	---

Environmental

Ambient Air Temperature For Operation	0...40 °C
---------------------------------------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Operating Altitude	0...3333 ft
Relative Humidity	0...95 %
Ambient Air Temperature For Storage	-15...40 °C
Storage Altitude	0.00...14999.82 m
Storage Relative Humidity	0...95 %

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	215 cm
Package 1 Width	106 cm
Package 1 Length	99 cm
Package 1 Weight	252 kg

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency

Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)