Product datasheet

Specification





Safety switch, heavy duty, non fusible, 60A, 3 wire, 3 pole, 60HP, 600V AC/DC, NEMA 3R, bolt on hub provision

HU362RB



Discontinued on: Sep 30, 2023 AD

① Discontinued

Main	
Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device Application	Heavy application
Disconnect Type	Non-fusible disconnect
Factory Installed Neutral	None
Network Number Of Phases	3 phases
Number Of Poles	3
Current Rating	60 A
Voltage Rating	600 V AC/DC
Enclosure Rating	NEMA 3R galvannealed steel
Motor Power Hp	10 hp at 240 V AC 5060 Hz for 1 phase motors 20 hp at 240 V AC 5060 Hz for 3 phases motors 25 hp at 480 V AC 5060 Hz for 1 phase motors 50 hp at 480 V AC 5060 Hz for 3 phases motors 30 hp at 600 V AC 5060 Hz for 1 phase motors 60 hp at 600 V AC 5060 Hz for 3 phases motors 10 hp at 250 V DC 30 hp at 600 V DC

Complementary

Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	3-wire
Wire Size	AWG 14AWG 3 copper AWG 12AWG 3 aluminium
Tightening Torque	5.65 N.m (AWG 3) 5.08 N.m (AWG 6AWG 4) 4.52 N.m for 8.367 mm² (AWG 8) 5.65 N.m for 2.065.261 mm² (AWG 14AWG 10)
Depth	162.05 mm
Width	266.70 mm
Height	539.75 mm
Net Weight	7 kg

Environment

Certifications UL listed file E2875

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.3 cm
Package 1 Width	28.5 cm
Package 1 Length	50.6 cm
Package 1 Weight	6.895 kg
Unit Type Of Package 2	PAL
Number Of Units In Package 2	40
Package 2 Height	115.57 cm
Package 2 Width	101.6 cm
Package 2 Length	121.92 cm
Package 2 Weight	293.02 kg

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free	
Ø	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations