# **Product datasheet**

Specifications





Ethernet switchboard display FDM128, up to 8 connected devices, screen 115.2 x 86.4mm, IP65 on front face

LV434128

#### Main

Device Short Name	FDM128	
Product Or Component Type	Display module	
Accessory / Separate Part Category	Display and signalling accessory	
Range Compatibility	MasterPact MTZ	
	MasterPact NW	
	MasterPact NT	
	Compact NSX	
	ComPact ComPact NS630b1600	
	ComPact ComPact NS1600b3200	
	PowerPact PowerPact H	
	PowerPact PowerPact J	
	PowerPact PowerPact L	
	PowerPact PowerPact P	
	PowerPact PowerPact R	
	Acti 9 Acti9 Smartlink smart communication module	
Product Name	Enerlin'X FDM	
Function Of Module	Remote control	
	View network	
	Metering	
	Display alarm	

### Complementary

Control Type	Remote control	
Mounting Mode	Flush mounting	
Mounting Support	Surface mount with kit	
Display Type	Active matrix colour TFT LCD with LED backlight	
Display Resolution	320 x 240 pixels QVGA	
View Angle Horizontal X Vertical	70 x 80°	
[Us] Rated Supply Voltage	24 V DC - 1520 %	
Power Consumption In W	6.8 W	
Standards	CE CSA UL	
Height	129 mm	
Width	163 mm	
Depth	56.5 mm	
Accessory / Separate Part Category	Spare part for ComPact NS630b1600 Spare part for ComPact NS1600b3200	

Spare part for ComPact NS630b...1600 Spare part for ComPact NS1600b...3200

## Environment

Ip Degree Of Protection	IP54 IP65 front face:
Ambient Air Temperature For Operation	-1055 °C

## **Packing Units**

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18.4 cm
Package 1 Width	6.8 cm
Package 1 Length	26.7 cm
Package 1 Weight	837.5 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	8
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	7.238 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	192
Package 3 Height	80 cm
Package 3 Width	120 cm
Package 3 Length	110 cm
Package 3 Weight	182.712 kg

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information