Product datasheet

Specification





Enclosed DOL starter, TeSys LG, 2.5-4A, 220/230V AC coil, including 1 LC1K, GV2ME, rotary isolation switch, 2 pushbuttons

LG1K065M708

Main

| Range | TeSys |
|-------------------------------------|----------------------------------------------------------------------------------------------------|
| Product Name | TeSys LG |
| Device Short Name | LG1K |
| Product Or Component Type | Enclosed DOL starter |
| Device Application | Safety |
| Utilisation Category | AC-3 |
| Device Composition | Contactor Switch disconnector Circuit-breaker |
| Motor Power Kw | 0.75 kW at 220/230 V AC 50/60 Hz 1.5 kW at 400/415 V AC 50/60 Hz 1.5 kW at 440 V AC 50/60 Hz |
| Thermal Protection Adjustment Range | 2.54 A |
| [Uc] Control Circuit Voltage | 220/230 V AC 50/60 Hz |
| Control Type | Push-button start white I Push-button stop black O Rotary handle emergency stop red |

Complementary

| Cable Entry Number | 4 2 Pg 13 + 2 Pg 16 top 4 2 Pg 13 + 2 Pg 16 bottom |
|--------------------|-------------------------------------------------------|
| Width | 175 mm |
| Height | 165 mm |
| Depth | 165 mm |
| Net Weight | 0.97 kg |

Environment

| Standards | IEC 60204-1 IEC 60947-4-1 |
|-------------------------------|------------------------------|
| Product Certifications | CE UKCA |
| Material | Polycarbonate |
| Ik Degree Of Protection | IK07 conforming to IEC 60529 |
| Ip Degree Of Protection | IP55 conforming to IEC 60529 |
| Environmental Characteristic | Standard environment |

19 Apr 2024 Life Is On Schneider

Packing Units

| 9 | |
|------------------------------|-----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 18.0 cm |
| Package 1 Width | 22.5 cm |
| Package 1 Length | 25.5 cm |
| Package 1 Weight | 1.741 kg |
| Unit Type Of Package 2 | P06 |
| Number Of Units In Package 2 | 12 |
| Package 2 Height | 77.0 cm |
| Package 2 Width | 80.0 cm |
| Package 2 Length | 60.0 cm |
| Package 2 Weight | 29.392 kg |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | End of Life Information |