Product datasheet

Specifications





Acti9 - fuse-disconnector STI - 3 poles - 25 A - for fuse 10.3 x 38 mm

A9N15656

Main

Range	Acti9
Product Name	Acti9 STI
Product Or Component Type	Fuse-disconnector
Device Short Name	STI
Poles Description	3P

Complementary

Complementary	
[In] Rated Current	2 A
	4 A
	6 A
	10 A
	16 A
	20 A
	25 A
Fuse Curve	GG
	AM
Fuse Size	10.3 x 38 mm
[Ue] Rated Operational Voltage	500 V AC
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	6
Height	81 mm
Width	54 mm
Depth	75 mm
Colour	White
Connections - Terminals	Screw clamp terminals1 cable(s) 0.7510 mm² rigid
	Screw clamp terminals1 cable(s) 0.56 mm ² flexible
	Screw clamp terminals2 cable(s) 0.754 mm ² rigid
	Screw clamp terminals2 cable(s) 0.56 mm ² flexible
Wire Stripping Length	12 mm
Tightening Torque	2 N.m

Environment

Standards	IEC EN 60947-3 IEC 60269-1/2
Ip Degree Of Protection	IP20

Pollution Degree	3
Ambient Air Temperature For Operation	-2060 °C
Ambient Air Temperature For Storage	-4080 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.500 cm
Package 1 Width	7.500 cm
Package 1 Length	8.500 cm
Package 1 Weight	165.800 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	4
Package 2 Height	8.500 cm
Package 2 Width	9.500 cm
Package 2 Length	22.500 cm
Package 2 Weight	709.000 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	48
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	8.925 kg

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations