## **Product datasheet**

Specification





# front display module - FDM 121 - 96 x 96 mm - IP54

TRV00121

#### Main

Device Short Name	FDM121	
Product Or Component Type	Display module	
Accessory / Separate Part Category	Display and signalling accessory	
Range Compatibility	MasterPact MTZ	
	MasterPact NW	
	MasterPact NT	
	Compact NSX	
	ComPact ComPact NS630b1600	
	ComPact ComPact NS1600b3200	
	PowerPact PowerPact H	
	PowerPact PowerPact J	
	PowerPact PowerPact L	
	PowerPact PowerPact P	
	PowerPact PowerPact R	
Product Name	Enerlin'X FDM	
Function Of Module	Remote control	
	View network	
	Metering	
	Display alarm	
	• •	

### Complementary

Control Type	Remote control
Mounting Mode	Flush mounting
Mounting Support	Surface mount with kit
	Door cut-out
Display Type	LCD screen with white backlighting
Display Resolution	128 x 128 pixels
View Angle Horizontal X Vertical	60 x 30°
[Us] Rated Supply Voltage	24 V DC - 2010 %
Current Consumption	21 mA
Standards	CE
	CSA
	UL
Height	96 mm
Width	96 mm
Depth	33.6 mm
Accessory / Separate Part Category	Spare part for ComPact NS630b1600 Spare part for ComPact NS1600b3200

#### **Environment**

Ip Degree Of Protection	IP53 front face:
Ambient Air Temperature For Operation	-1055 °C
Ambient Air Temperature For	-4085 °C

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.803 cm
Package 1 Width	10.275 cm
Package 1 Length	10.375 cm
Package 1 Weight	244.5 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	34
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	8967 g
Unit Type Of Package 3	P12
Number Of Units In Package 3	816
Package 3 Height	95 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	224208 g

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>②</b>	Mercury Free	
	Rohs Exemption Information	Yes
	Pvc Free	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information