

Acti9 - comb busbar - 1L+N - 18 mm pitch - 24 modules - 100 A



Main

Range	Acti9	
Product Or Component Type	Comb busbar	
Mounting Mode	Horizontal	
Accessory / Separate Part Category	Connection accessory	
Lines Description	1L + N	
Length In 18 Mm Modules	24	

Complementary

Number Of Ways	12 ways N + 1 L	
Poles Configuration For 1 Way	1 x 1P + N 1 x 2P	
Connection Pitch	18 mm	
Connector Type	Tooth	
Distance Between Way	36 mm	
Marking	N L	
Insulation	Insulated	
Device Presentation	Cuttable	
[le] Rated Operational Current	100 A at 40 °C	
[Ue] Rated Operational Voltage	415 V AC	
[Ui] Rated Insulation Voltage	500 V AC conforming to IEC 61439-2	
Mounting Location	Top or bottom on tunnel type terminals Top or bottom on double terminal	
9 Mm Pitches	48	
Width	430 mm	
Colour	White (RAL 9003)	
Range Compatibility	Acti 9 Acti9 iC60 Acti 9 Acti9 iK60 Acti 9 Acti9 iID Acti 9 Acti9 iID K Acti 9 Acti9 iSW Acti 9 Acti9 iSW-NA Multi9 Multi9 C60	

Environment

Standards	IEC 60947-7-1	
	IFC 61439-2	

Fire Resistance	960 °C (30 s) conforming to IEC 60695-2-1
Pollution Degree	3 conforming to IEC 60947-7-1
Ip Degree Of Protection	IP20 with end-nieces and tooth covers

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	5.600 cm	
Package 1 Width	8.400 cm	
Package 1 Length	46.600 cm	
Package 1 Weight	166.000 g	
nit Type Of Package 2 BB1		
Number Of Units In Package 2	n Package 2 5	
Package 2 Height	5.600 cm	
Package 2 Width	8.400 cm	
Package 2 Length	46.600 cm	
Package 2 Weight	934.000 g	
Unit Type Of Package 3	S04	
Number Of Units In Package 3	55	
Package 3 Height	30.000 cm	
Package 3 Width	3 Width 40.000 cm	
Package 3 Length	60.000 cm	
Package 3 Weight	11.147 kg	

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations