# **Product datasheet**

Specifications

#### Green Premium™



## Acti9 - fuse-disconnector STI - 1 pole - 10 A - for fuse 8.5 x 31.5 mm

A9N15635

#### Main

Range	Acti9
Product Name	Acti9 STI
Product Or Component Type	Fuse-disconnector
Device Short Name	STI
Poles Description	1P

## Complementary

Complementary	
[In] Rated Current	2 A
	4 A
	6 A
	10 A
Fuse Curve	AM
	GG
Fuse Size	8.5 x 31.5 mm
[Ue] Rated Operational Voltage	400 V AC
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	2
Height	81 mm
Width	18 mm
Depth	75 mm
Colour	White
Connections - Terminals	Screw clamp terminals1 cable(s) 0.7510 mm² rigid
	Screw clamp terminals1 cable(s) 0.56 mm² flexible
	Screw clamp terminals2 cable(s) 0.754 mm² rigid
	Screw clamp terminals2 cable(s) 0.56 mm² flexible
Wire Stripping Length	12 mm
Tightening Torque	2 N.m

#### Environment

Standards	IEC EN 60947-3 IEC 60269-1/2
Ip Degree Of Protection	IP20
Pollution Degree	3

Ambient Air Temperature For Operation	-2060 °C
Ambient Air Temperature For Storage	-4080 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.8 cm
Package 1 Width	7.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	55 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.6 cm
Package 2 Width	9.2 cm
Package 2 Length	22.2 cm
Package 2 Weight	714 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	144
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	9.055 kg

# Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations