# **Product datasheet**

Specification





# 16 A X/20 A 2 Gang 1 way full - flat switch with ON indicator White

E8432\_1\_WE

### Main

| Range                     | ZENcelo                       |
|---------------------------|-------------------------------|
| Product Or Component Type | Switch                        |
| Device Application        | Control                       |
| Load Type                 | Incandescent lamp Resistive   |
|                           | Fluorescent lamp<br>Inductive |

# Complementary

| Device Mounting  | Surface<br>Flush   |
|------------------|--|
| Switch Function  | 1-way  |
| Rated Current    | 20 A/16 AX at 250 V AC 50 Hz   |
| Local Signalling | Mechanical indicator, neon (amber)   |
| Number Of Gangs  | 2 gangs  |
| Material         | Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: cover Polycarbonate: surround |

# **Packing Units**

| Unit Type Of Package 1       | PCE      |
|------------------------------|----------|
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 3.5 cm   |
| Package 1 Width              | 8.7 cm   |
| Package 1 Length             | 8.7 cm   |
| Package 1 Weight             | 125.84 g |
| Unit Type Of Package 2       | S04      |
| Number Of Units In Package 2 | 80       |
| Package 2 Height             | 30 cm    |
| Package 2 Width              | 40 cm    |
| Package 2 Length             | 60 cm    |
| Package 2 Weight             | 8.434 kg |
| Unit Type Of Package 3       | P12      |
| Number Of Units In Package 3 | 1600     |

| Package 3 Height | 125 cm    |  |
|------------------|-----------|--|
|                  | 123 UII   |  |
| Package 3 Width  | 105 cm    |  |
|                  |           |  |
| Package 3 Length | 80 cm     |  |
| Package 3 Weight | 170.28 kg |  |



Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

| <b>Ø</b> | Reach Free Of Svhc         |     |
|----------|----------------------------|-----|
| <b>⊘</b> | Toxic Heavy Metal Free     |     |
| <b>Ø</b> | Mercury Free               |     |
| <b>⊘</b> | Rohs Exemption Information | Yes |

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Compliant EU RoHS Declaration   |
| China Rohs Regulation    | China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | No need of specific recycling operations  |