Product datasheet





MOUNTING PLATE TARIF CLASS 2 INV+NSX250 WIDTH 600/650

03145

! Discontinued on: 9 Aug 2023

① Discontinued

EAN Code: 3303430031451

Main

Range	Prisma
Range Of Product	Prisma G Prisma P
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P cubicle
Installation Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 + 150 mm depth 400 mm Cubicle - width 650 mm depth 400 mm
Mounting Plate Description	Insulating
Installed Device	ComPact: fixed INV160 - control: direct front rotary handle - vertical installation ComPact: fixed INV200 - control: direct front rotary handle - vertical installation ComPact: fixed NSX100160 with earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX250 with earth leakage protection - control: toggle - vertical installation ComPact: fixed INV100 - control: toggle - vertical installation ComPact: fixed INV160 - control: toggle - vertical installation ComPact: fixed INV200 - control: toggle - vertical installation ComPact: fixed INV250 - control: toggle - vertical installation
Poles Description	1 x 4P: fixed INV250 vertical installation 1 x 4P: fixed INV100 vertical installation 1 x 4P: fixed INV160 vertical installation 1 x 4P: fixed INV200 vertical installation 1 x 4P: fixed NSX100160 vertical installation 1 x 4P: fixed NSX250 vertical installation
Number Of Vertical Modules [50 Mm]	12 module(s): NSX100160 with earth leakage protection , direct in 600 mm Widefloor-standing enclosure 12 module(s): NSX100160 with earth leakage protection , direct in 600 mm Widewall-mounted enclosure 12 module(s): NSX250 with earth leakage protection , direct in 650 + 150 mm Widecubicle
Standards	NF C 15-100 IEC 61439-2

Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Matt Smooth
Colour	White (RAL 9001)
Width	600 mm

Life Is On Schneider 25 Apr 2024

200 mm
1.28 kg
600 mm Prisma G floor-standing enclosure ComPact INV100 fixed toggle vertical 4P 1 direct 137.5 mm 600 mm Prisma G wall-mounted enclosure ComPact INV100 fixed toggle vertical 4P 1 direct 137.5 mm 600 mm Prisma G floor-standing enclosure ComPact INV160 fixed toggle vertical 4P 1 direct 125 mm 600 mm Prisma G wall-mounted enclosure ComPact INV160 fixed toggle vertical 4P 1 direct 125 mm 650 mm 400 mm Prisma P cubicle ComPact INV160 fixed direct front rotary handle vertical 4P 1 direct 137.5 mm 600 mm Prisma G floor-standing enclosure ComPact INV200 fixed toggle vertical 4P 1 direct 125 mm 600 mm Prisma G wall-mounted enclosure ComPact INV200 fixed toggle vertical 4P 1 direct 125 mm 650 mm 400 mm Prisma P cubicle ComPact INV200 fixed direct front rotary handle vertical 4P 1 direct 137.5 mm 600 mm Prisma G floor-standing enclosure ComPact INV250 fixed toggle vertical 4P 1 direct 125 mm 600 mm Prisma G wall-mounted enclosure ComPact INV250 fixed toggle vertical 4P 1 direct 125 mm 600 mm Prisma G wall-mounted enclosure ComPact INV250 fixed toggle vertical 4P 1 direct 125 mm 600 mm Prisma G floor-standing enclosure ComPact INV250 fixed toggle vertical 4P 1 direct 125 mm 600 mm Prisma G floor-standing enclosure ComPact NSX100160 with fixed toggle vertical 4P 1 direct 12 125 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX100160 with fixed toggle vertical 4P 1 direct 12 125 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX100160 with fixed toggle
vertical 4P 1 direct 12 125 mm 650 + 150 mm 400 mm Prisma P cubicle ComPact NSX250 with fixed toggle vertical 4P 1 direct 12 137.5 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	19.500 cm
Package 1 Length	47.000 cm
Package 1 Weight	1.280 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	10
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	13.580 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	80
Package 3 Height	75.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	108.640 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
Ø	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile