



# CLASS 2 INSULATING PLATE WIDTH 600/650

03154

! Discontinued on: 25 Apr 2023

EAN Code: 3303430031543

! Discontinued

#### Main

Range	Prisma
Range Of Product	Prisma G Prisma P
Product Or Component Type	Insulating plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P cubicle
Installation Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm Pack enclosure - width 555 mm
Installed Device	Power meters: kilowatt-hour meters - vertical installation
Poles Description	2 x 4P: kilowatt-hour meters vertical installation 3 x 2P: kilowatt-hour meters vertical installation
Number Of Vertical Modules [50 Mm]	9 module(s): kilowatt-hour meters in 600 mm Widefloor-standing enclosure 9 module(s): kilowatt-hour meters in 600 mm Widewall-mounted enclosure 9 module(s): kilowatt-hour meters in 650 mm Widecubicle 9 module(s): kilowatt-hour meters in 555 mm WidePack enclosure 6 module(s): kilowatt-hour meters in 600 mm Widefloor-standing enclosure 6 module(s): kilowatt-hour meters in 600 mm Widewall-mounted enclosure 6 module(s): kilowatt-hour meters in 650 mm Widecubicle 6 module(s): kilowatt-hour meters in 555 mm WidePack enclosure
Standards	IEC 61439-2
Product Certifications	ASEFA

# Complementary

Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Matt Smooth
Colour	White (RAL 9001)
Width	600 mm
Height	420 mm
Net Weight	0.66 kg

#### **Functional Unit**

600 mm Prisma G floor-standing enclosure power meters kilowatt-hour meters

vertical 2P 3 6

600 mm Prisma G wall-mounted enclosure power meters kilowatt-hour meters

vertical 2P 3 6

600 mm Prisma G floor-standing enclosure power meters kilowatt-hour meters vertical 4P 2 9

600 mm Prisma G wall-mounted enclosure power meters kilowatt-hour meters vertical 4P 2 9

650~mm~400~mm Prisma P cubicle power meters kilowatt-hour meters vertical 2P 3 6650 mm 400 mm Prisma P cubicle power meters kilowatt-hour meters vertical 4P 2 9

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	52.0 cm
Package 1 Length	68.0 cm
Package 1 Weight	670.0 g
Unit Type Of Package 2	P12
Number Of Units In Package 2	24
Package 2 Height	81.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	28.8 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>②</b>	Rohs Exemption Information Yes
<b>Ø</b>	Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile