Product datasheet

Specification





RECESSED SLOTTED M.PLATE W600 4M

03171

! Discontinued on: 5 Apr 2023

EAN Code: 3303430031710

Main

Range	Prisma	
Range Of Product	Prisma G	
Product Or Component Type	Mounting plate	
Accessory / Separate Part Category	Installation accessory	
Range Compatibility	Prisma Prisma G enclosure	
Installation Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm	
Mounting Plate Description	Recessed slotted	
Installed Device	Phaseo: LV/LV transformer	
Number Of Vertical Modules [50 Mm]	4 module(s): LV/LV transformer in 600 mm Widefloor-standing enclosure 4 module(s): LV/LV transformer in 600 mm Widewall-mounted enclosure	
Standards	IEC 61439-2	
Product Certifications	ASEFA	

Complementary

Surface Finish	Galvanized	
Width	600 mm	
Height	200 mm	
Net Weight	0.74 kg	
Functional Unit	600 mm Prisma G floor-standing enclosure Phaseo LV/LV transformer 4 12.5 mm 600 mm Prisma G wall-mounted enclosure Phaseo LV/LV transformer 4 12.5 mm	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	18.5 cm
Package 1 Length	46.5 cm
Package 1 Weight	800.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	20.0 cm

Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	8.1 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	120
Package 3 Height	105.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	97.92 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
⊘	Rohs Exemption Information Yes
⊘	Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile