
# **Product datasheet**





## FRONT PLATE INF63 V.4P-INF160 V.3/4P WIDTH 600/650 5M

03315

! Discontinued on: 31 Dec 2020

(!) Discontinued EAN Code: 3303430033158

### Main

Range	Prisma	
Range Of Product	Prisma G Prisma P	
Product Or Component Type	Front plate	
Accessory / Separate Part Category	Installation accessory	
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P cubicle	
Type Of Front Plate	Cut-out	
Installed Device	FuPact: fixed INF63 - control: extended rotary handle - vertical installation FuPact: fixed INF100160 - control: extended rotary handle - vertical installation	
Poles Description	2 x 3P: mounting plate support: INF100160 vertical installation 2 x 4P: mounting plate support: INF100160 vertical installation 2 x 4P: mounting plate support: INF63 vertical installation	
Operating Position	Vertical	

## Complementary

•	
Enclosure/Cubicle Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm
Connection Position	Direct connection
Number Of Vertical Modules [50 Mm]	5
Standards	IEC 61439-1 IEC 61439-2
Product Certifications	ASEFA
Material	Steel
Surface Finish	Smooth Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	250 mm
Width	500 mm
Net Weight	1.04 kg
Quantity Per Set	Set of 1

Life Is On Schneider 25 Apr 2024



#### **Functional Unit**

600 mm Prisma G floor-standing enclosure FuPact INF100...160 fixed extended rotary handle vertical 3P 2 direct 7

600 mm Prisma G wall-mounted enclosure FuPact INF100...160 fixed extended rotary handle vertical 3P 2 direct 7

600 mm Prisma G floor-standing enclosure FuPact INF100...160 fixed extended rotary handle vertical 4P 2 direct 7

600 mm Prisma G wall-mounted enclosure FuPact INF100...160 fixed extended rotary handle vertical 4P 2 direct 7

650 mm 400 mm Prisma P cubicle FuPact INF100...160 fixed extended rotary handle vertical 3P 2 direct 5

650 mm 400 mm Prisma P cubicle FuPact INF100...160 fixed extended rotary handle vertical 4P 2 direct 5

600~mm Prisma G floor-standing enclosure FuPact INF63 fixed extended rotary handle vertical 4P 2 direct 5

600 mm Prisma G wall-mounted enclosure FuPact INF63 fixed extended rotary handle vertical 4P 2 direct 5

650 mm 400 mm Prisma P cubicle FuPact INF63 fixed extended rotary handle vertical 4P 2 direct 5

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm
Package 1 Width	26 cm
Package 1 Length	51 cm
Package 1 Weight	1.05 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>Ø</b>	Halogen Free Plastic Parts Product

### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile