# **Product datasheet**

Specifications





# FRONT PLATE ISFT 630 VERTICAL W650 8M

03324

! Discontinued on: 8 Jul 2022

EAN Code: 3303430033240

(!) Discontinued

#### Main

Range	Prisma	
Range Of Product	Prisma P	
Product Or Component Type	Front plate	
Accessory / Separate Part Category	Installation accessory	
Range Compatibility	Prisma Prisma P cubicle	
Type Of Front Plate	Cut-out	
Installed Device	FuPact: fixed ISFT630 - control: fuse carriers handle - horizontal installation	
Poles Description	1 x 3P: mounting plate support: ISFT630 horizontal installation	
Operating Position	Horizontal	

### Complementary

Enclosure/Cubicle Description	Cubicle - width 650 mm depth 400 mm
Connection Position	Direct connection
Number Of Vertical Modules [50 Mm]	8
Standards	IEC 61439-1 IEC 61439-2
Product Certifications	ASEFA
Material	Steel
Surface Finish	Smooth Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	400 mm
Width	500 mm
Net Weight	1.62 kg
Quantity Per Set	Set of 1
Functional Unit	650 mm 400 mm Prisma P cubicle FuPact ISFT630 fixed fuse carriers handle horizontal 3P 1 direct 10

### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	3.000 cm
Package 1 Width	50.000 cm
Package 1 Length	51.000 cm
Package 1 Weight	1.610 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	10.500 cm
Package 2 Width	50.500 cm
Package 2 Length	52.000 cm
Package 2 Weight	10.361 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	36
Package 3 Height	47.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	72.840 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile