# **Product datasheet**





### TRANSPARENT FRONT PLATE WIDTH 600/650 9M

03344

! Discontinued on: 5 Apr 2023

EAN Code: 3303430033448

! Discontinued

#### Main

Range	Prisma	
Range Of Product	Prisma G Prisma P	
Product Or Component Type	Front plate	
Accessory / Separate Part Category	Installation accessory	
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P cubicle	
Type Of Front Plate	Transparent	
Installed Device	Power meters: kilowatt-hour meters - vertical installation	
Poles Description	2 x 4P: mounting plate support: kilowatt-hour meters vertical installation 2 x 3P: mounting plate support: kilowatt-hour meters vertical installation	

#### Complementary

<b>Complementary</b>	
Enclosure/Cubicle Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm Pack enclosure - width 555 mm
Number Of Vertical Modules [50 Mm]	9
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA
Material	Glass
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	450 mm
Width	500 mm
Net Weight	2.04 kg
Quantity Per Set	Set of 1
Functional Unit	600 mm Prisma G floor-standing enclosure power meters kilowatt-hour meters vertical 4P 2 9 600 mm Prisma G wall-mounted enclosure power meters kilowatt-hour meters

650 mm 400 mm Prisma P cubicle power meters kilowatt-hour meters vertical 4P 2 9

Life Is On Schneider 19 Apr 2024

vertical 4P 2 9

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.000 cm
Package 1 Width	45.000 cm
Package 1 Length	50.000 cm
Package 1 Weight	2.040 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	25.000 cm
Package 2 Width	47.000 cm
Package 2 Length	52.000 cm
Package 2 Weight	12.240 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	12
Package 3 Height	43.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	28.480 kg

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>Ø</b>	Reach Free Of Svhc	
<b>②</b>	Toxic Heavy Metal Free	
<b>9</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile