# **Product datasheet**

Specification





## FR.PL.NS3200

03716

! Discontinued on: 9 Aug 2023

EAN Code: 3303430037163

① Discontinued

#### Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Type Of Front Plate	Cut-out
Installed Device	ComPact: fixed NS1600b - control: toggle - vertical installation ComPact: fixed NS20003200 - control: toggle - vertical installation
Poles Description	1 x 3P: mounting plate support: NS1600b vertical installation 1 x 4P: mounting plate support: NS1600b vertical installation 1 x 3P: mounting plate support: NS20003200 vertical installation 1 x 4P: mounting plate support: NS20003200 vertical installation
Operating Position	Horizontal

# Complementary

Francisco (Oubiala Dagarintian	0.1:1:111.050
Enclosure/Cubicle Description	Cubicle - width 650 mm depth 400 mm
	Cubicle - width 650 mm depth 600 mm
Connection Position	Front connection
Number Of Vertical Modules [50 Mm]	8
Standards	IEC 61439-1
	IEC 61439-2
Product Certifications	ASEFA
Material	Steel
Surface Finish	Smooth
	Matt
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	400 mm
Width	500 mm
Net Weight	1.02 kg
Quantity Per Set	Set of 1

Functional Unit 650 mm 400 mm Prisma P cubicle ComPact NS1600b fixed toggle vertical 3P 1 front

connection on adaptor 14

650 mm 400 mm Prisma P cubicle ComPact NS1600b fixed toggle vertical 4P 1 front

connection on adaptor 14

650~mm 600~mm Prisma P cubicle ComPact NS2000...3200 fixed toggle vertical 3P 1

front connection on adaptor 16

650 mm 600 mm Prisma P cubicle ComPact NS2000...3200 fixed toggle vertical 4P 1

front connection on adaptor 16

## **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	41.0 cm
Package 1 Length	51.0 cm
Package 1 Weight	1.03 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	48
Package 2 Height	49.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	60.64 kg

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc
<b>⊘</b>	Toxic Heavy Metal Free
<b>⊘</b>	Mercury Free
<b>⊘</b>	Rohs Exemption Information Yes
<b>⊘</b>	Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information