

# Product datasheet

Specifications



## VARPLUSCAN HORIZONTAL MOUNTING PLATE

03979

! Discontinued on: 9 Aug 2023

EAN Code: 3606480687198

! Discontinued

### Main

Range	Prisma
Range Of Product	Prisma P
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma P cubicle
Installation Description	Cubicle - width 650 + 150 mm depth 400 mm
Provided Equipment	Gasket not included
Mounting Location	Bottom of enclosure VarPlus Can VarplusCan first 480 mm Bottom of enclosure VarPlus Can VarplusCan second 325 mm Bottom of enclosure VarPlus Can VarplusCan + detuned reactors first 155 mm Bottom of enclosure VarPlus Can VarplusCan + detuned reactors second 300 mm
Mounting Plate Description	Dedicated
Installed Device	Power factor correction: fixed VarPlus Can - horizontal installation
Number Of Vertical Modules [50 Mm]	36 module(s): VarPlus Can in 650 + 150 mm Widecubicle (cable coming from top or bottom of enclosure)
Standards	IEC 61439-2 IEC 61439-1
Product Certifications	ASEFA

### Complementary

Colour	White (RAL 9001)
Width	550 mm
Height	235 mm
Depth	365 mm
Net Weight	0 kg
Functional Unit	650 + 150 mm 400 mm Prisma P cubicle power factor correction VarPlus Can fixed horizontal 4 36 0.1 mm

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.000 cm
Package 1 Width	24.000 cm

<b>Package 1 Length</b>	55.000 cm
<b>Package 1 Weight</b>	5.290 kg
<b>Unit Type Of Package 2</b>	S04
<b>Number Of Units In Package 2</b>	4
<b>Package 2 Height</b>	30.000 cm
<b>Package 2 Width</b>	40.000 cm
<b>Package 2 Length</b>	60.000 cm
<b>Package 2 Weight</b>	21.160 kg
<b>Unit Type Of Package 3</b>	P12
<b>Number Of Units In Package 3</b>	48
<b>Package 3 Height</b>	105.000 cm
<b>Package 3 Width</b>	80.000 cm
<b>Package 3 Length</b>	120.000 cm
<b>Package 3 Weight</b>	265.920 kg

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

---

✓ Toxic Heavy Metal Free

---

✓ Mercury Free

---

✓ Rohs Exemption Information Yes

---

✓ Halogen Free Plastic Parts Product

---

## Certifications & Standards

**Eu Rohs Directive** Pro-active compliance (Product out of EU RoHS legal scope)  
[EU RoHS Declaration](#)

---

**China Rohs Regulation** [China RoHS declaration](#)  
Pro-active China RoHS declaration (out of China RoHS legal scope)

---

**Environmental Disclosure** [Product Environmental Profile](#)

---

**Circularity Profile** [End of Life Information](#)

---