
Product datasheet

Specifications





LINERGY TA AUXIL.TERM.BLK 10 IN/20 OUT

04228

! Discontinued on: 5 Apr 2023

EAN Code: 3303430042280

Main

Range	Linergy	
Range Of Product	Linergy	
Product Or Component Type	Terminal block	
Product Name	Linergy TA	
Accessory / Separate Part Category	Connection accessory	
Range Compatibility	Linergy Linergy TA auxiliary connector Prisma Prisma G enclosure Prisma Prisma P cubicle	
Product Compatibility	Auxiliary connection	

Complementary

Enclosure/Cubicle Description	Cubicle Floor-standing enclosure Wall-mounted enclosure	
[le] Rated Operational Current	12 A (40 °C) at 250 V AC conforming to IEC 20 A (40 °C) at 300 V AC conforming to UL	
Tightening Torque	0.50.6 N.m	
Connections - Terminals	- Terminals Input: screw terminal 10 pin(s) 0.24 mm² rigid without cable end Output: removable screw terminal block 20 pin(s) 0.24 mm² flexible with cable end	
Conductor Material	Copper	
Quantity Per Set	t Set of 1	
Height	50 mm	
Width	65 mm	
Depth	50 mm	
Net Weight	0.12 kg	
Colour	Light grey (RAL 7035)	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	5.0 cm
Package 1 Length	5.0 cm

19 Apr 2024 Life Is On Schneider

Package 1 Weight	110.0 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	50
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	6.34 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information