Product datasheet

Specification





discrete input module Modicon Quantum - 16 I - 10..60 V DC

140DDI84100C

! Discontinued on: 9 Feb 2023

EAN Code: 3595861136649

! Discontinued

Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	Dc discrete input modules
Discrete Input Number	16

Complementary

oompromentary		
Group Of Channels	8	
Logic Input	Positive (sink)	
Input Voltage Limits	1060 V	
Input Voltage	12 V 510 mA DC 24 V 630 mA DC 48 V 215 mA DC 60 V 15 mA DC	
Voltage State 1 Guaranteed	1124 V 24 V +/- 20 % 3448 V 48 V +/- 20 % 4560 V 60 V +/- 20 % 912 V 12 V +/- 5 %	
Voltage State 0 Guaranteed	01.8 V 12 V +/- 5 % 010 V 48 V +/- 20 % 05 V 24 V +/- 20 % 09 V 60 V +/- 20 %	
Absolute Maximum Voltage	75 V	
Addressing Requirement	1 input word	
Response Time	4 ms from state 0 to state 1 4 ms from state 1 to state 0	
Switching Frequency	<= 100 Hz	
Isolation Between Group And Bus	2500 Vrms DC for 1 minute	
Isolation Between Group	700 Vrms DC for 1 minute	
Power Dissipation	1 W + (0.62 x number of points on)	
Marking	CE	
1 LED (green) for bus communication is present (Active) 1 LED (red) for external fault detected (F) 16 LEDs (green) for input status		
Bus Current Requirement	200 mA	
Module Format	Standard	
Net Weight	0.3 kg	

25 Apr 2024 Life Is On Schneider

Environment

Protective Treatment	Conformal coating Humiseal 1A33	
Standards	CSA C22.2 No 142 UL 508	
Product Certifications	FM Class 1 Division 2 C-Tick	
Resistance To Electrostatic Discharge	4 kV contact conforming to IEC 801-2 8 kV on air conforming to IEC 801-2	
Resistance To Electromagnetic Fields	10 V/m 802000 MHz conforming to IEC 801-3	
Ambient Air Temperature For Operation	060 °C	
Ambient Air Temperature For Storage	-4085 °C	
Relative Humidity	95 % without condensation	
Operating Altitude	<= 5000 m	

Packing Units

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	16.3 cm
Package 1 Width	4.5 cm
Package 1 Length	31.2 cm
Package 1 Weight	468.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	2
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	1.2 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
Ø	Mercury Free	
Ø	Rohs Exemption Information	Yes


Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks




- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots

Connections and Schema

60 Vdc Discrete Input Sink Module

Wiring Diagram



N/C Not Connected