

# Product datasheet

Specifications



## voltage release - iMX - tripping unit - 12..24 VAC

Local distributor code: 396737265 A9A26478

### Main

Range of product	Acti 9
Product or component type	Shunt trip release
Device short name	IMX
[Uc] control circuit voltage	12...24 V AC 50/60 Hz 12...24 V DC
9 mm pitches	2

### Complementary

Range compatibility	Acti9 iC65 Acti 9 ARA Acti9 iDPN Vigj Acti9 iID Acti9 iSW-NA Acti 9 RCA Acti 9 iDPN (China version) Acti9 iC60 Acti 9 iC40
Local signalling	Action indicator
Mounting mode	Clip-on
Mounting support	DIN rail
Width	18 mm
Colour	White
Connections - terminals	Clamp terminal - 2 cable(s) 2.5 mm <sup>2</sup> - flexible with cable end Clamp terminal - 1 cable(s) 6 mm <sup>2</sup> - rigid Clamp terminal - 2 cable(s) 2.5 mm <sup>2</sup> - rigid Clamp terminal - 1 cable(s) 4 mm <sup>2</sup> - flexible
Tightening torque	1 N.m
Compatibility code	IMX

### Environment

Standards	EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	76 g
Package 1 Height	8 cm
Package 1 width	2.8 cm
Package 1 Length	9.3 cm
Unit Type of Package 2	S03
Number of Units in Package 2	72
Package 2 Weight	6.55 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	8
Package 3 Weight	671 g
Package 3 Height	8.6 cm
Package 3 width	9.8 cm
Package 3 Length	26.5 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------