

Product datasheet

Specifications



voltage release - iMNs - tripping unit - 220..240 VAC

TSI Code: 396737126 A9A26963

Main

Range of product	Acti 9
Product or component type	Undervoltage release
Device short name	IMNs
[Uc] control circuit voltage	220...240 V AC 50/60 Hz
Control type	Delayed
9 mm pitches	2

Complementary

Range compatibility	Acti 9 iC65 Acti 9 ARA Acti 9 iDPN Vigi Acti 9 iLD Acti 9 iSW-NA Acti 9 RCA Acti 9 iDPN (China version) Acti 9 iC60 double terminals miniature circuit breaker Acti 9 iC40
Local signalling	Action indicator
Mounting mode	Clip-on
Mounting support	DIN rail
Width	18 mm
Colour	White
Connections - terminals	Clamp terminal - 1 cable(s) 10 mm ² - rigid Clamp terminal - 2 cable(s) 2.9 mm ² - rigid Clamp terminal - 1 cable(s) 8 mm ² - flexible Clamp terminal - 2 cable(s) 2.9 mm ² - flexible with cable end
Tightening torque	1 N.m
Compatibility code	IMNs

Environment

Standards	EN/IEC 60947-5-1
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...50 °C

Ambient air temperature for storage	-40...85 °C
-------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	81 g
Package 1 Height	3 cm
Package 1 width	8 cm
Package 1 Length	9.4 cm
Unit Type of Package 2	S03
Number of Units in Package 2	72
Package 2 Weight	6.882 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	8
Package 3 Weight	710 g
Package 3 Height	9 cm
Package 3 width	26.5 cm
Package 3 Length	10 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------