Product datasheet

Specifications





switch Acti9 iSW - 4 poles - 20 A - 415V

Local distributor code: 399367784

A9S60420

EAN Code: 3606480088704

Main

Range	Acti9	
Product Name	Acti9 iSW	
Product Or Component Type	Switch disconnector	
Device Short Name	iSW	
Device Application	Control	
Poles Description	4P	
Utilisation Category	AC-22A	
Suitability For Isolation	Yes	

Complementary

· · · · · · · · · · · · · · · · · ·	
[le] Rated Operational Current	20 A at 415 V AC 50/60 Hz
[Ue] Rated Operational Voltage	415 V AC 50/60 Hz
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz conforming to EN/IEC 60669-2-4
[Uimp] Rated Impulse Withstand Voltage	4 kV
Control Type	Toggle
Local Signalling	ON/OFF indication
Contact Position Indicator	Yes
Mounting Mode	Fixed
Mounting Support	DIN rail
9 Mm Pitches	4
Height	77 mm
Width	36 mm
Depth	70 mm
Colour	White
Mechanical Durability	300000 cycles
Electrical Durability	30000 cycles
Connections - Terminals	Tunnel type terminals - 10 mm² - rigid Tunnel type terminals - 10 mm² - flexible Tunnel type terminals - 10 mm² - flexible with ferrule
Wire Stripping Length	9 mm
Tightening Torque	1.2 N.m

Environment

Standards	EN/IEC 60669-2-4	
Ip Degree Of Protection	IP4	
Pollution Degree	2	
Tropicalisation	2	
Relative Humidity	95 % at 55 °C	
Ambient Air Temperature For Operation	-2050 °C	
Ambient Air Temperature For Storage	-4070 °C	

Packing Units

J	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7 cm
Package 1 Width	3.5 cm
Package 1 Length	7.9 cm
Package 1 Weight	131 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	8.1 cm
Package 2 Width	9.5 cm
Package 2 Length	23 cm
Package 2 Weight	834 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	72
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	10.495 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information